


Precision slit (entrance and exit slit)



The precision slit assembly is a backlash free spring pivot system allowing an accurate symmetric and parallel opening and closing of the two slit jaws. It is driven by one single linear feedthrough. This precision feedthrough can be chosen as manual or motorized type. The motorized type is driven by a stepper motor.

The slit assembly is mounted on a CF150 base flange which has fiducial holes on its air side for alignment and surveying.

Water cooling of the slit jaws and / or their electrical insulation for drain current measurements are possible options.

The slit chamber has a nominal size of 150CF and can contain several other ports for a pre-aperture, viewports, fluorescent screens and an ion pump a.s.o..

The whole slit chamber can be moved along the beam direction by a manual or stepper-motor-driven precision linear guide system. The necessary length compensation is realised with welded bellows upstream and downstream of the slit chamber.

The linear guide system is supported by a rigid steel frame support or a block made of concrete or granite. The support contains elevation and lateral adjustment elements. They allow an accurate alignment of the slit system with respect to the beam axis.

FMB GmbH

FMB Feinwerk- und Meßtechnik GmbH
Friedrich Wöhler Strasse 2
D - 12489 Berlin
Germany

Phone : +49 (0) 30 67 77 30 - 0
Fax : +49 (0) 30 67 77 30 - 40
E-mail : info@fmb-berlin.de
www.fmb-berlin.de



Precision slit (entrance and exit slit)

Technical Data.

Slit subassembly

- Slit opening range 0...3 mm
- Repeatability of the slit opening < 3 μ m
- Step size of the slit opening (with stepper motor linear feedthrough) < 1 μ m / step
- Slit jaw length 30 mm
- Slit jaw parallelism < 3 μ m

Linear system for travel parallel to the beam

- Beam direction stroke Up to \pm 500 mm
- Positioning accuracy \pm 0.2 mm
- Travelling accuracy \pm 10 μ m

Support

- Elevation and lateral adjustment range of the adjustment elements \pm 10 mm
- Adjusting elements accuracy \pm 0.05 mm

Nominal width of ports

- Pump flange DN 100 CF
- Entry and exit flange or membrane bellows DN 35 CF
Option: DN 63 CF

Slit cooling

- Indirect water cooling using flexible copper braids as Option

Drain current measurement

- Using floating shields feedthroughs and Aluminium-Nitride insulation as Option

FMB GmbH